

UniQ Hohlwand Geräte-V-Dose 73 mm, luftdicht, halogenfrei



- ❖ Einsatz als Geräteverbindungsdose, Gerätedose, Elektronikdose und Großrohrdose
- ❖ Deutlich mehr Klemmraum durch Ø 74 mm
- ❖ Werkzeuglose Rohr- und Kabeleinführung
- ❖ SCS-Verbindungstechnik = feste Verbindung und einfache Durchverdrahtung ohne Verbindungsstutzen
- ❖ 4x3 Schraubdome für flexible Ausrichtung der Geräte
- ❖ Sichere Fixierung durch Leitungsrückhaltung
- ❖ Geeignet für Plattenstärke 25 mm
- ❖ Membrantechnik mit Rohrgrip für sichere Zugentlastung



Artikelnummer	P270-01
Kategorie	Hohlwandinstallation
Montageart	-
EAN	4260182067239
Material Dose	PP
Material Einführungen	TPE
Farbe	Grün-orange

Produkteigenschaften

Durchmesser	74 mm
Tiefe	73 mm
Schraubdome	4x3
Anzahl Kabeleinführungen	15
Anzahl Rohreinführungen	1x bis M20, 3x bis M25, 1x bis M32
Querschnitt (1,5 mm) ohne Gerät	7 Klemmen, 21 Leiter
Querschnitt (2,5 mm) ohne Gerät	5 Klemmen, 15 Leiter
Querschnitt (1,5 mm) mit Gerät	5 Klemmen, 15 Leiter
Querschnitt (2,5 mm) mit Gerät	4 Klemmen, 12 Leiter

UniQ cavity wall C-box 73 mm, airtight, halogen-free



- ❖ Used as appliance junction box, appliance box, electronics box and large conduit box
- ❖ Significantly more clamping space thanks to Ø 74 mm
- ❖ Tool-free conduit and cable entry
- ❖ SCS connection technology = fixed connection and simple through-wiring without connecting pieces
- ❖ 4x3 screw bosses for flexible alignment of the devices
- ❖ Secure fixing thanks to cable retention
- ❖ Suitable for panel thickness 25 mm
- ❖ Membrane technology with pipe grip for secure strain relief



Article No.	P270-01
Category	cavity wall
Type of installation	-
EAN	4260182067239
Material case	PP
Material conduit entries	TPE
Colour	Green-orange

Product features

Diameter	74 mm
Depth	73 mm
Screw domes	4x3
Number of cable entries	15
Number of conduit entries	1x up to M20, 3x up to M25, 1x up to M32
Cross-section (1.5 mm) without device	7 clamps, 21 conductors
Cross-section (2.5 mm) without device	5 clamps, 15 conductors
Cross-section (1.5 mm) with device	5 clamps, 15 conductors
Cross-section (2.5 mm) with device	4 clamps, 12 conductors